

E-Move

130 kg user

NiMH battery

<input type="checkbox"/>	20"	MEM20
<input type="checkbox"/>	22"	MEM22
<input type="checkbox"/>	24"	MEM24
<input type="checkbox"/>	25"	MEM25
<input type="checkbox"/>	26"	MEM26

150 kg Heavy Duty user

NiMH battery

<input type="checkbox"/>	20"	MEM20-HD 150
<input type="checkbox"/>	22"	MEM22-HD 150
<input type="checkbox"/>	24"	MEM24-HD 150
<input type="checkbox"/>	25"	MEM25-HD 150
<input type="checkbox"/>	26"	MEM26-HD 150

Li-ion battery

<input type="checkbox"/>	20"	MEML20
<input type="checkbox"/>	22"	MEML22
<input type="checkbox"/>	24"	MEML24
<input type="checkbox"/>	25"	MEML25
<input type="checkbox"/>	26"	MEML26

Li-ion battery

<input type="checkbox"/>	20"	MEML20-HD 150
<input type="checkbox"/>	22"	MEML22-HD 150
<input type="checkbox"/>	24"	MEML24-HD 150
<input type="checkbox"/>	25"	MEML25-HD 150
<input type="checkbox"/>	26"	MEML26-HD 150

Standard version includes two power supported wheels . NTP tyres. Two stainless steel push rims.

On/off button to the right. Battery and battery charger.

Information regarding the wheelchair

Manufacturer: _____

Model: _____

Seat width: _____

Brackets: _____

Visit our website for updated overview brackets.

<http://decon.se/en/adapters/>

Battery positions

See in our adapter list which battery position is possible for your wheel chair.

MEM1478

MEM1477

MEM1700

Second profile



MEM7600

With this option, there is an extra button the wheelchair. You are able to switch between two pre programmed (individual) settings. For example inside or outside driving characteristic

Power converter



MED12V

Charge your battery in your car, boat, caravan or camper van output 230V AC 50Hz 150W

Upgrade to coated push rims

Upgrade the standard push rims (Stainless steel) to Polymer compact, foamed or Max Grip.



MEM7651- Polymer compact

MEM7652- Foamed

MEM7653- Max grip

Transparent spoke guard

Prevent your finger from injury.



20" SG2007

22" SG2207

24" SG2407

25" SG2507

26" SG2607

Tyres

Solid puncture proof tyres



NarrowTreadPattern(NTP)

PU With NTP

NTP/Flexible Inner tub

DF2011

20" DP2002

DF2011/MS201

DF2212

22" DP2202

DF2212/MS221

DF2411

24" DP2402

DF2411/MS241

DF2511

25" X

DF2511/MS251

DF2611

26" DP2602

DF2611/MS261

|
|
|
|
|

—
—
—

MO
S.

ie
11
10
10
10
10